



VM-3 and VM-5 valve manifolds

✓ Body material – steel (316 ss)





VM-5 valve




VM-3 valve

Features

3-valve and 5-valve manifolds are used where relative pressure transmitters are installed. They enable essential operations to be performed on the transmitters, such as starting up a transmitter or setting the zero position in conditions of static or atmospheric pressure. The five-valve manifold also enables a calibrator to be connected for metrological testing of the transmitter. The VM-3 and VM-5 have a modern lightweight construction. The high precision of manufacture enables individual valves to be opened and closed easily.





Weldable connector for impulse line made from: stainless steel 316Lss /1/ K11562 steel /2/



Connector for impulse line, made from 316ss stainless steel with a clamping ring:



Ø12 /3/
Ø14 /4/




Technical parameters

Maximum pressure	420 bar (according to the graph)
Pin packing	PTFE or graphite
Body material	316ss
Weight: VM-3	1.8 kg
VM-5	2.54 kg
Connectors:	
to the installation	– ½ NPT sockets
to the transmitter	– 54 mm spacing

Connection diagrams




Example of installation of the VM-3 with fitting accessories



Special versions


Versions R



Versions H



Operating pressure range as a function of temperature



Recommendations concerning selection of valves

The standard versions of the valves have Teflon pin packing; a special version is available with graphite packing. The special version should be used only when the valves operate at temperatures in excess of 200°C.

The valve manifold is supplied with seals for the collar-type output points. To order, it can be supplied additionally with a set of M10 or 7/16" (stainless steel) screws for fitting the transmitter, connectors for impulse lines and a sheet-metal handle used to mount the valve on the construction.

Ordering procedure

Valve manifolds:

3-valve – **VM-3** / / /

5-valve – **VM-5** / / /

Special versions:

H – constructional versions (only VM-3)

R – constructional versions

Graphite – graphite pin packing

Tlen – valve adapted to contact with oxygen

Code

Product

A	Set of M10 screws for fitting the transmitter
B	Set of 7/16" × 1" screws for fitting the transmitter
C	Set of 7/16" × 2 ¼" screws for fitting the transmitter with covers type COPLANAR
1	Set of weldable stainless steel connectors (316ss)
2	Set of weldable steel connectors (K11562)
3	Set of connectors with Ø12 clamping ring
4	Set of connectors with Ø14 clamping ring
U	Handle for mounting the valve

Additional equipment – description: